

10/2025

Plug & play disinfection devices for laboratories and clinics

Touch-free, UV-free and chemical-free disinfection
with visible blue light

Spectral Blue by LED Tailor Oy
Joensuunkatu 7, Salo, Finland
Web: <https://spectral.blue>
Email: info@ledtailor.com
Tel.: +358 44 766 91 00



Plug & play blue light disinfection devices

Spectral Blue MWHI® Multi-Wavelength, High-Intensity blue light technology.



SALO




OSLO




BERLIN




HELSINKI



Biosafety cabinets,
laminar hoods



Workbenches, equipment,
machines




Whole rooms,
working areas

Whole rooms,
working areas

	SALO/XL	OSLO	BERLIN	HELSINKI
POWER	55 W / 105 W	102 W	202 W	230 W
PLACEMENT	Cabinet	Wall or ceiling	Mobile	Mobile
BEAM ANGLE	180°	120°	120°	360°
CORD LENGTH	1 m	3 m	3 m	3 m
DIMENSIONS	L604 / L1160 x H66 x W109 mm	L657 x H59 x W90 mm	L304 x H1236 x W304 mm	ø 470 (base) x H1532 mm
WEIGHT	2.2 kg / 4 kg	2.8 kg	8,7 kg	10 kg

Effective ranges and disinfection times

Range and efficiency data are based on independent laboratory tests with *Escherichia coli*.



Continuous disinfection keeps your facilities clean 24/7

Which devices to choose? The longer you can use blue light during the day, the less power you need – contact us to let our experts help.

